

Active Visual Mate

Function Setting Controller

【Specifications】

Model	Active Visual Mate
Controllable functions:	
<Gain>	1. Selectable AGC range from 6 to 30dB in 1dB steps 2. Manual fixed gain selectable from 6 to 30dB in 1dB steps
<Shutter speed>	1. EI (Min. & Max. speed range can be selected manually from OFF (1/60(N) or 1/50(P)), FL (1/120(N) or 1/100(P)), 1/250, 1/500, 1/1000, 1/2500, 1/5000, 1/10000, 1/20000, 1/50000, 1/100000) 2. ES (Shutter speed can be selected manually from OFF, FL, 1/250, 1/500, 1/1000, 1/2500, 1/5000, 1/10000, 1/20000, 1/50000, 1/100000)
<Back light>	Selectable from 5 area settings
<Setup level>	Controllable within a range of 0 to 7.5IRE
<Video level>	Selectable either 75IRE or 100IRE
<White balance>	1. ATW 2. Fixed (Color temperature can be selected from 3200K, 4400K, 5100K, and 8200K. RED & BLUE gain can be finely adjusted separately as well.)
<Gamma>	Selectable either 0.45 or OFF
<Outline enhancer>	Selectable from OFF, SOFT, NORMAL, HARD for both horizontal and vertical
<Others>	Picture color selection (Color/Monochrome), Mirror image (ON/OFF), Data save/delete
Display	Transflective STN LCD
Back light	Yellow-green LED
Power supply	DC+6V±10% (Use of power supply AD-603 or dry cell batteries (AA×4) is recommended.)
Battery life	≒8h (Display light ON), ≒100h (Display light OFF)
Current	50mA (Back light ON)
operating temperature	0°C - +50°C (w/o condensation)
Storage temperature	-10°C - +60°C (w/o condensation)
Dimension	80 (W) × 88 (H) × 41 (D) mm
Weight	330g
Accessories	AD-603 (Power supply), cable (1m)

【Dimensions】 (mm)

